GRYPHON™ 4500 HEALTHCARE

CDATALOGIC

Premium handheld scanners for corded or cordless value added Healthcare applications



THE PURPOSE OF BAR CODE READERS IN THE HEALTHCARE INDUSTRY

The key mission of scanners in the healthcare industry is to improve the quality of patient care while reducing medication errors. Additionally, healthcare environments have requirements that scanners need to be regularly cleaned and disinfected. The Datalogic Gryphon™ HC product series is specifically developed for healthcare applications with Disinfectant-Ready enclosures treated with antimicrobial additives and are designed to withstand daily cleaning with harsh disinfectant solutions.

The Gryphon 4500-HC 2D readers can decode virtually any 1D and 2D bar code symbology and can read codes from LCD monitors, cell phones, smartphones and other mobile devices. High Density (HD) models are also available for reading smaller, condensed codes.

Ideally suited for stationary applications in administration, laboratory and hospital environments, the GD4500-HC 2D desktop model offers an affordable corded solution, while the GM4500-HC 2D or GBT4500-HC 2D cordless models (STAR or Bluetooth®) provide extended mobility for cordless operations.

Datalogic's distinctive reading technology with highly visible white or red-illumination is easier on the human eyes and reads colored labels better. The highly visible 4-Dot aimer provides a clear indication of the reading area, making targeting codes quick and easy. Datalogic's patented 'Green Spot' technology provides additional visual good-read confirmation which is ideal for quiet environments such as bedside patient care.

The vibration option coupled with the silent operating mode can also be set to further increase the patients' comfort.

One of the most important technical innovations that the Gryphon 4500 wireless readers achieve is the wireless charging system for the battery, which enhances the reliability of the entire solution, while lowering the total cost of ownership (no need for contact cleaning or maintenance procedures).

FEATURES

- Disinfectant-Ready enclosures treated with anti-microbial additives (ISO22196 compliant) withstand daily cleaning with harsh disinfectant solutions
- 1 MP optics for superior scanning and Depth of Field
- Extended reading distances and snappy reading of small, condensed, curved, poorly printed, and reflective bar codes
- Highly visible 4-Dot aimer with center cross for targeted scanning
- Datalogic's 'Green Spot' technology, exclusive 3GL™ (3 Green Lights) and Vibration for superior good-read feedback
- Motionix[™] motion-sensing technology for seamless reading mode transitions
- Image capture and document scanning capabilities
- Omnidirectional reading of 1D, 2D and postal codes plus stacked, composite codes and dot codes
- Choice of Bluetooth wireless technology version or Datalogic's STAR Cordless System (radio frequencies available in 433 MHz or 910 MHz)
- Wireless battery charging system
- Choice of WLC4090 adjustable position cradle with Scan-While-Charging capability or WLC4190 sleek desk/wall cradle with USB Type C connectivity

















PRODUCT	CHEMICAL CONTENT	
Sani-Cloth® HB, Sani-Cloth® Plus, Super Sani-Cloth®	Quaternary Ammonium Chloride solution	
Hepacide Quat II	Virucidal disinfectant cleaner	
Alcohol Wipes	70% Isopropyl Alcohol	
CaviWipes™	Isopropanol 10-20%; Ethylene Glycol Monobutyl Ether 1-5%	
Virex® 256	n-Alkyl Dimethyl Benzyl Ammo- nium Chloride; Didecyl Dimethyl Ammonium Chloride	
Formula 409® Glass and Surface Cleaner	n-Alkyl Dimethyl Benzyl Ammoni- um Chloride; n-Propoxypropanol	
Windex® Blue	Isopropyl Alcohol	
Clorox® Bleach; Clorox Healthcare Bleach Germicidal Cleaner	Sodium Hypochlorite; Sodium Hydroxide	
Hydrogen Peroxide	3%	
ProSpray™ Wipes (Disinfectant towelettes)	0.647% o-phenylphenol; 0.070% o-benzyl-p-chlorophenol	
100% Gentle dish soap and water		

GRYPHON 4500 HEALTHCARE SERIES

TECHNICAL SPECIFICATIONS

	Rhietooth Wireless Technology	Colors Available	Plack White (with light groop placetic/gubbar details)	
Bluetooth Wireless Technology Piconet: Max. 7 readers per radio receiver (cradle and commercial dongle); Profiles: HID (Human Interface Device); SPP (Serial Port Profile); Protocol: Bluetooth 5.0 Certified Class 1, Class 2 and Class 3; Radio Frequency: 2.4 GHz; Radio Range (Open Air): 100.0 m / 328.0 ft; Range distances are measured using the base station. Range with connection to other Bluetooth peripherals may show different results. Security: Data Encryption; Scanner Authentication	Dimensions	Black, White (with light green plastic/rubber details) 16.6 x 6.8 x 10.9 cm / 6.5 x 2.7 x 4.3 in (corded/cordles models)		
	Certified Class 1, Class 2 and Class 3; Radio Frequency:	Weight	161 g / 5.7 oz (corded models); 235 g / 8.29 oz (cordless models, battery included)	
	Enclosure	Disinfectant-Ready enclosure treated with anti-microl additives (ISO22196 compliant)		
	READING PERFORM	RMANCE		
Datalogic STAR Cordless System Effective Radiated Power: 433.92 MHz: < 6.3 mW; 910 MHz: < 50 mW; Multi-Point Configuration: Max. Readers per Radio Receiver: 16; Point-to-Point Configuration; Radio Frequency: 433.92 MHz; 910 MHz; Two Way Communications Radio Range (Open Air): 50.0 m / 164.0 ft		Image Capture	Graphic Formats: BMP, JPEG, TIFF; Greyscale: 256, 1	
	Imager Sensor	1 Megapixel: 1280 x 800 pixels		
	Light Source	Aiming: Red Laser 650 nm Illumination: Warm White; Hyper Red LED on specific models		
AECODING CADADU		Motion Tolerance	35 IPS	
ECODING CAPABII		Print Contrast Ratio (Minimu	m) 15%	
ID / Linear Codes	Auto discriminates all standard 1D codes including GS1 DataBar™ linear codes.	Reading Angle	Pitch: +/- 65°; Roll (Tilt): 360°; Skew (Yaw): +/- 65°	
?D Codes	Aztec Code; China Han Xin Code; Data Matrix; MaxiCode; Micro QR Code; QR Code; Dot Code	Reading Indicators	Beeper (adjustable tone); Datalogic Three Green Light (3GL) Good-read feedback: Datalogic 'Green Spot' on Code, Dual Good-read LEDs; Vibration feedback optio	
Postal Codes	Australian Post; British Post; China Post; IMB; Japanese Post; KIX Post; Planet Code; Postnet; Royal Mail Code (RM4SCC)		available on cordless models High Density (HD): 1D Linear: 0.077 mm / 3 mils; PDF417: 0.077 mm / 3 mils;	
Stacked Codes	EAN/JAN Composites; GS1 DataBar Composites; GS1 DataBar Expanded Stacked; GS1 DataBar Stacked; GS1 DataBar Stacked Omnidirectional; MacroPDF; MicroPDF417; PDF417; UPC A/E Composites	Resolution (Maximum) Data Matrix: 0.102 mm / 4 mils Standard Range (SR): 1D Linear: 0.102 mm / 4 mil PDF417: 0.127 mm / 5 mils; Data Matrix: 0.195 mm / 7.5 mils		
ORDLESS MODELS	S ELECTRICAL	READING RANGE	S	
Battery	Battery Type: Lithium-Ion: 3250 mAh Charge Time: External Power: 4 Hours @ 12 VDC; Reads per Charge: 80,000	Typical Depth of Field	Minimum distance determined by symbol length and angle. Printing resolution, contrast, and ambient light dependent.	
Cradle Indicator LEDs	Battery Charging (flashing orange); Charge Completed (steady green)	Standard Range (SR) Code 39: 5 mils: 7.0 to 38.0 cm / 2.7 to 14.9 in Code 39: 10 mils: 2.2 to 58.0 cm / 0.8 to 22.8 in Data Matrix: 10 mils: 5.5 to 27.0 cm / 2.2 to 10.6 in Data Matrix: 15 mils: 2.8 to 41.0 cm / 1.1 to 16.1 in EAN/UPC: 13 mils: 2.5 to 41.0 cm / 1.0 to 16.1 in PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 to 16.1 in EAN/UPC: 13 mils: 1.0 to 64.0 cm / 0.4 to 27.9 in EAN/UPC: 13 mils: 1.0 to 64.00 cm / 0.4 to 27.9 in EAN/UPC: 14 mils: 15 mils: 15 to 25.0 to 25.0 cm / 0.4 to 27.9 in EAN/UPC: 14 mils: 15 to 25.0 to 25.0 cm / 0.4 to 27.9 in EAN/UPC: 15 mils		
Current	Charging (Typical): < 6 W; Scanner only: 330 mA @ 3.7 V (Operative) Cradle only: 80 mA @ 5 V (Operative)			
nput Voltage (Cradle)	4.5 - 14 VDC +/- 5% (WLC4090/WLC4190)			
ORDED MODELS E	LECTRICAL	QR Code: 10 mils: 5.5 to 24.0 cm /	2.2 to 9.5 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in	
Current	Operating: <400 mA @ 5V; < 200 mA @ 12V Standby/Idle: < 90 mA @ 5V; <50 mA @ 12V	PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12 QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9		
nput Voltage	GD4520: 5 VDC; GD4590: 4.5 - 14.0 VDC	SAFETY & REGUL	ATORY	
NVIRONMENTAL			The product meets necessary safety and regulatory approvals for its intended use.	
Ambient Light	0 - 100,000 lux	Agency Approvals	The Quick Reference Guide for this product can be	
Orop Resistance	Withstands repeated drops from 1.8 m / 6.0 ft onto a concrete surface.	Environmental Compliance	referred to for a complete list of certifications.	
ESD Protection (Air Discharge)	16 kV		Caution Laser Radiation - Do not stare into beam;	
Humidity (Non-Condensing)	0 - 95%	Laser Classification	IEC 60825 Class 2	
Particulate and Water Sealing	IP52	UTILITIES		
Temperature	Operating: 0 to 50 °C / 32 to 122 °F Storage/Transport: -40 to 70 °C / -40 to 158 °F	Datalogic Aladdin™	Datalogic Aladdin configuration program is available download at no charge.	
NTERFACES		OPOS / JavaPOS	JavaPOS and OPOS Utilities are available for downloa at no charge.	
Interfaces WI WI Int	CORDLESS MODELS: WLC4090: USB / RS-232 / Keyboard Wedge Multi-Interface	Remote Host Download	Lowers service costs and improves operations	
	WLC4190: USB Type C / USB / RS-232 / Keyboard Wedge Multi- Interface	WARRANTY		
	CORDED MODELS: GD4520: USB type C / USB only	Warranty	5-Year Factory Warranty (corded models) 3-Year Factory Warranty (cordless models)	

ACCESSORIES

Base Stations / Chargers

DS-GRYPHON4500-HC-SERIES-EN Rev G 20230223











Mounts / Stands





